

Gamma Series

Gamma 60

Procedure & Exam Light



Gamma 60 is a global leader in exam lighting and offers a high intensity of 60,000 Lux at 18". The luminaire features an optically advanced 50-watt IRC (infrared coated) halogen-xenon bulb, which provides a long 3000 hour bulb life and 3400K color temperature. It is ideal for medical examinations.

Features:

Fitted With: 1 x halogen lamp QR-CBC51 50 W

Luminous Power: 60,000 Lux / 18" (0.5m)

Work Equipment: Electronic plug-in transformer

Connected Load: 120V; 50/60 Hz

Mains Lead:

- Approx. 118" (3m) cordset with hospital grade plug
- Approx. 47" (1.2m) coiled cord with hospital grade plug for single ceiling mounted light

Luminaire Body: Polycarbonate (PC)

Weight (NET):

- Approx. 3.3 lbs (1.5kg) for rail and wall mounted lights
- Approx. 19.8 lbs (9.0kg) for single ceiling mounted light
- Approx. 30.5 lbs (13.8kg) for floor stand light

Power Consumption: Approx. 50 W

Usage: Rocker switch (I/O)

Technology: 2-pole primary

Class Of Protection: II

Accessory: Color correction filter (ca. 4100 K)

Norms: EN 60601-1, EN 60601-2-41

Fastening:

- Ceiling mount included (23.5"-39.4" extensible) for ceiling mounted light
- Rail mount included for rail mounted light
- Wall mount included for wall mounted light
- Floor stand included for floor stand light
- Table mount included for table mounted light



Dimensions



Model Examples

L-GA60-AB-CX-X	Gamma 60, Articulating Arm, Basic, Single Ceiling Mount
L-GA60-EB-RH-A	Gamma 60, Articulating Arm w/Extension, Basic, Rail Mount, Horizontal, Amico
L-GA60-GB-RH-A	Gamma 60, Gooseneck Arm, Basic, Rail Mount, Horizontal, Amico
L-GA60-IB-RV-F	Gamma 60, Gooseneck Arm w/Extension, Basic, Rail Mount, Vertical, Fairfield

NOTE: North American: 120 V; International: 230 V

Ordering Guide

- AB:** Articulating Arm, Basic
- EB:** Articulating Arm with Extension
- GB:** Gooseneck Arm, Basic
- IB:** Gooseneck Arm with Extension

L-GA60- - -

- RH:** Rail Mount, Horizontal
- RV:** Rail Mount, Vertical
- FX:** Floorstand
- WX:** Wall Mount
- CX:** Ceiling Mount
- TX:** Table Mount
- A:** Amico Rail (For Rail Mount Only)
- F:** Fairfield Rail (For Rail Mount Only)
- X:** Not Applicable